



Pass and Seymour
PlugTail® Specification Grade 15A Duplex Self-Test Feed-Through GFCI Receptacles with SafeLock® Protection, Gray
Part No. PT1597FTGRY



15A PlugTail® GFCI with feed through is designed for fast, safe, and consistent installation across any job site. It works with both 3-wire PlugTail® connectors and 5-wire connectors, supporting non-feed-through and feed-through wiring to protect downstream receptacles. A finger-safe design eliminates exposed terminals, enhancing safety before, during, and after installation. UL-listed connectors ensure proper orientation, while the PlugTail® modular system delivers predictable, time-saving installation regardless of installer skill level. This GFCI extends the proven PlugTail® platform by adding feed-through capability, enabling broader application coverage with the same installation efficiency.

Features & Benefits

Conducts an automatic self-test every three seconds to ensure continuous protection. If SafeLock® Protection disconnects power to the receptacle if critical components the device fails the test, the indicator light alerts that the GFCI should be replaced are damaged and protection is lost

Enables faster, more reliable installation using the PlugTail® modular wiring system, delivering consistent results across all skill levels. No exposed terminals create a fully finger-safe application before, during, and after installation

Built-in connector interface features large brass terminal blades for consistent, dependable electrical connection to PlugTail® connectors

Designed to work with both 3-wire tails and 5-wire tails, enabling non-feed-through and feed-through wiring for downstream GFCI protection in a modular format

Supports streamlined prefabrication and jobsite productivity by maintaining the familiar PlugTail® workflow while expanding application capability

Durable zinc-plated steel mounting strap provides strength and long-term reliability in demanding commercial environments

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007502657	Country Of Origin	China
Number of Receptacles	2	Features	Feed Through, Self-Test
Outlet Type	GFCI, Tamper-Resistant	Application Sector	Commercial
Wall Plate Included	Yes	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.74 in	Product Depth US	1.65 in
Product Height US	4.2 in	Product Length US	4.2 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Connection Location	Back Only	Number of Wires	3
Amperage	15 A	Number of Poles	2 Pole

Indoor/Outdoor	Indoor	Wire Connection Type	PlugTail
Voltage	125.0 V		