



20A PlugTail® GFCI with feed through is designed for fast, safe, and consistent installation across any job site. It works with both 3-wire PlugTail® connectors and 5-wire connectors, supporting non-feed-through and feed-through wiring to protect downstream receptacles. A finger-safe design eliminates exposed terminals, enhancing safety before, during, and after installation. UL-listed connectors ensure proper orientation, while the PlugTail® modular system delivers predictable, time-saving installation regardless of installer skill level. This GFCI extends the proven PlugTail® platform by adding feed-through capability, enabling broader application coverage with the same installation efficiency.

Features & Benefits

Conducts an automatic self-test every three seconds to ensure continuous protection. If the device fails the test, the indicator light alerts that the GFCI should be replaced	SafeLock® Protection disconnects power to the receptacle if critical components are damaged and protection is lost
Enables faster, more reliable installation using the PlugTail® modular wiring system, delivering consistent results across all skill levels.	No exposed terminals create a fully finger-safe application before, during, and after installation
Built-in connector interface features large brass terminal blades for consistent, dependable electrical connection to PlugTail® connectors	Designed to work with both 3-wire tails and 5-wire tails, enabling non-feed-through and feed-through wiring for downstream GFCI protection in a modular format
Supports streamlined prefabrication and jobsite productivity by maintaining the familiar PlugTail® workflow while expanding application capability	Durable zinc-plated steel mounting strap provides strength and long-term reliability in demanding commercial environments

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007502732	Country Of Origin	China
Number of Receptacles	2	Features	Feed Through, Self-Test
Outlet Type	GFCI, Tamper-Resistant	Application Sector	Commercial
Wall Plate Included	Yes	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.74 in	Product Depth US	1.65 in
Product Height US	4.2 in	Product Length US	4.2 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Connection Location	Back Only	Number of Wires	3
Amperage	20 A	Number of Poles	2 Pole

Indoor/Outdoor	Indoor	Wire Connection Type	PlugTail
Voltage	125.0 V		