



Pass and Seymour
PlugTail® Connectors, Right Angle, Five wire, Stranded, 6-in
Part No. PTR6STR5W



PlugTail® 5-Wire Connector, Right angle, #12 AWG, THHN, 6" pre stripped copper conductors, stranded. Built for feed-through wiring applications, the UL-listed connector ensures correct orientation and consistent terminations with PlugTail® receptacles, while the finger-safe, right-angle housing enhances safety and installation speed. Stranded leads allow smooth handling and improved maneuverability on dense commercial layouts.

Features & Benefits

Ultrasonically welded polycarbonate housing provides a secure, finger-safe enclosure for all terminations

#12 AWG, 6" THHN stranded copper leads engineered exclusively for PlugTail® receptacles.

Pre-stripped leads and PlugTail® interface simplify installation, delivering more consistent, reliable connections than standard pigtails

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007502763	Country Of Origin	China
Features	Feed Through	Application Sector	Commercial
Wall Plate Included	Yes	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.47 in	Product Depth US	1.04 in
Product Height US	6.0 in	Product Length US	6.0 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Energy Savings	No		
Technical Information			
Connection Location	Back Only	Number of Wires	5
Indoor/Outdoor	Indoor	Wire Connection Type	PlugTail
Voltage	125.0 V		