



Pass and Seymour
Digital Timer Switch, 100-300VAC/0-800/1200W, White
Part No. WTS12W



The IntelliSwitch WTS12W series digital time switches automatically turn lights off after a preset time.

Features & Benefits

Optional audible or visual alerts before lights turn off

Terminal style wiring for simplified installation

Digital operation and simple pushbutton set-up

Time scroll features allows timer to adjust up or down

Automatically turns lights off after preset time

Bright electroluminescent LCD shows timer's countdown

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007502497
Country Of Origin	China	Material	Plastic
Features	Single Display, Timer	Switch Type	Push
Installation Location	Wall Box	Application Sector	Commercial
Warranty Type	5-Year	Type	Timer

Dimensions

Product Width US	1.8 in	Product Depth US	1.8 in
Product Height US	4.2 in		

Additional Information

Product Has Potential to Contribute to LEED	Yes	Energy Savings	Yes
---	-----	----------------	-----

Technical Information

Operating Temperature Min	32 °F	Load Rating	1200 W @ 277 VAC, 800 W @ 120 VAC
Operating Temperature Max	104 °F	Number of Buttons	1
Timer Duration	1-12 Hours, 5-60 Minutes	Indicator	Selectable audible alert for impending shutoff
Input Voltage	120/277 VAC	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	On Function	Manual On
Operating Temperature	32°-104°F	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	Flying Leads		