



Pass and Seymour  
Heavy Duty, Short Length, Rotating Eye, K-Type  
Part No. PS0501

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 0.500-0.610-inch, Mesh Length - 11-inch, Eye Diameter - 7/8-inch, Break Strength- 5,600 lbs.



## Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 11: Eye Diameter: 7/8

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007993776
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Pulling Grip		

### Dimensions

Mesh Length	16 in	Cable Diameter Range	0.500-0.620 in
-------------	-------	----------------------	----------------

### Technical Information

Approximate Break Strength	5600 lb	Maximum Cable Range	0.5 in
Eye Style	Rotating	Minimum Cable Range	0.61 in

---

Capacity

Various Cable Diameter Ranges

Indoor/Outdoor

Both

---

Mounting

Consult the Factory for Mounting  
Recommendations

---