



Pass and Seymour
Heavy Duty, Short Length, Rotating Eye, K-Type
Part No. PS1001

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 1.000-1.240-inch, Mesh Length - 20-inch, Eye Diameter - 1 3/8-inch, Break Strength - 16,400 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 20: Eye Diameter: 1-3/8

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007994100
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Pulling Grip		

Dimensions

Mesh Length	30.7 in	Cable Diameter Range	1.00-1.50 in
-------------	---------	----------------------	--------------

Technical Information

Approximate Break Strength	12800 lb	Maximum Cable Range	1 in
Eye Style	Rotating	Minimum Cable Range	1.24 in

Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations		