



Pass and Seymour

Industrial Extra Heavy Duty Specification Grade Switch, Lighted When On, Back and Side Wire, Red

Part No. PS15AC1RPL

1-Pole Pilot Lighted Switch, Back and Side-Wire, 15A 120V



Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Impact- and chemical-resistant cover.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Auto-ground clip assures positive ground.

Cam control and spring actuator for positive "makes and breaks."

Heavy-duty bumpers for quiet, smooth operation.

Locking support provides resistance to face and back body separation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Grounding terminal is standard with screw-pressure plate back wire.

Shallow design for easier installation.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007195804
Country Of Origin	Mexico	Application Sector	Commercial

Standard

UL20, FEDSPEC

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	15Amp, 120/277Vac	Amperage	15 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG