



Pass and Seymour  
Industrial Extra Heavy Duty Specification Grade Switch, Clear  
Part No. PS15AC3CSL



1-Pole Lighted Switch, Back and Side-Wire, 15A 120/277V

## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-grounded clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Clear
UPC Number	785007195712	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 20, FEDSPEC

### Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	15Amp, 120/277Vac	Amperage	15 A
----------------	-------------------	----------	------

Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
-----------------	-------------	-----------	---------------

Wattage	3 W
---------	-----