



Pass and Seymour
 Discontinued - Industrial Extra Heavy Duty Specification Grade Switch, Light Almond
 Part No. PS15AC4LA



4way Toggle Switch, Back & Side Wire, 15amp 120/277volt, Light Almond

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 20

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Technical Information

Actuator	Toggle	Contact Rating	120/277vac, 15amp
Amperage	15 A	Action	DPDT
Number of Poles	Double Pole	Voltage	120.0 V
