



Pass and Seymour
Extra Heavy Duty Spec. Grade and Security Switches
Part No. PS20AC2KL



2-Pole Key Lock Back and Side-Wire 20A 120/277V

Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc.

Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007195668
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20, FEDSPEC	Type	Switch

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Wire Size	#14 - #10 AWG	Wattage	2 W
Voltage	120.0 V		