



2-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V

## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007195330
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 20, FEDSPEC		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	20 Amp, 120/277 VAC	Amperage	20 A
Number of Poles	Double Pole	Wire Size	#14 - #10 AWG
Wattage	2 W		