



400A 600V, Cable Size #2 - 2/0, Female Cam-Type Plug, Green

Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance	Exceptional seal for maintaining NEMA Type 3R and 4 integrity
Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product	Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
Heavy-duty hex set screws allow greater termination torque	Copper wire provides quality strain relief
Copper shim bundles wire strands to reduce "splaying."	

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL, cCSAus		

Technical Information

Amperage	400 A	Number of Poles	Single Pole
Wire Size	2/0	Voltage	600.0 V
Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4		