



Pass and Seymour  
Series 16 In-Line Connectors  
Part No. PS20FBR



400A 600V, Cable Size #2 - 2/0, Female Cam-Type Plug, Green

## Features & Benefits

|                                                                                                                                          |                                                                                                   |
|------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|
| Thermoplastic elastomer housing for outstanding impact and chemical resistance                                                           | Exceptional seal for maintaining NEMA Type 3R and 4 integrity                                     |
| Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product | Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity |
| Heavy-duty hex set screws allow greater termination torque                                                                               | Copper wire provides quality strain relief                                                        |
| Copper shim bundles wire strands to reduce "splaying."                                                                                   |                                                                                                   |

## Specifications

### General Info

|                    |                        |                   |            |
|--------------------|------------------------|-------------------|------------|
| Product Line       | Pass & Seymour         | Color             | Red        |
| UPC Number         | 785007308129           | Country Of Origin | Mexico     |
| Application Sector | Commercial, Industrial | Standard          | UL, cCSAus |

### Technical Information

|                          |                                                                                                                                       |                 |             |
|--------------------------|---------------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------|
| Amperage                 | 400 A                                                                                                                                 | Number of Poles | Single Pole |
| Wire Size                | 2/0                                                                                                                                   | Voltage         | 600.0 V     |
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact:<br>Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |                 |             |