Pass and Seymour
Heavy Duty, Short Length, Rotating Eye, K-Type
Part No. PS3001

Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 3.00-3.490-inch, Mesh Length - 30-inch, Eye Diameter - 1 7/8-inch, Break Strength - 48,000 lbs.

Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

Mesh Length: 30: Eye Diameter: 1-7/8

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007994155
Country Of Origin	Mexico	Product Type	Cord Grip
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Dimensions

Mesh Length	40.9 in	Cable Diameter Range	3.00-3.50 in

Technical Information

Approximate Break Strength	41000 lb	Maximum Cable Range	3 in
Eye Style	Rotating	Minimum Cable Range	3.49 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both

Mounting	Consult the Factory for Mounting Recommendations