



Pass and Seymour Heavy-Duty, Standard Length, Rotating Eye, K-Type Part No. PS3002

Heavy-Duty, Standard Length, Rotating Eye, K-Type. Cable Diameter - 3.000-3.490", Mesh Length - 39", Eye Diameter - 1 7/8", Break Strength - 41,000 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel. They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Specifications

General Info

UPC Number	785007994421	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval [consult factory]

Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 3.000-3.490; Mesh Length: 39; Eye Diameter: 1-7/8
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 41,000