



Pass and Seymour  
Replacement Cover for Standard Switch, 30A  
Part No. PS30SSRC

Replacement cover for use with Non-Fusible Safety Switch PS30SS.

## Product Image Coming

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL, CSA		

#### Dimensions

Product Width US	4.9 in	Product Depth US	6.52 in
Product Height US	8.4 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Technical Information

Contact Configuration	(Optional) 1 N.O. & 1 N.C.	Contact Rating	(Optional) 10A @ 600VAC
Amperage	30 A	Voltage	600.0 V

---

Environmental Conditions	Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability: Flammability: UL94 5VA and V0 Classification: UV Resistance: All enclosure materials are UV stable
--------------------------	---

---