



Pass and Seymour
Heavy Duty, Short Length, Rotating Eye, K-Type
Part No. PS3501



Heavy-Duty, Short Length, Rotating Eye, K-Type. Cable Diameter - 3.500-3.990-inch, Mesh Length - 32-inch, Eye Diameter - 1 7/8-inch, Break Strength - 48,000 lbs.

Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Mesh Length: 32: Eye Diameter: 1-7/8

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 48000		