

Canadian 1-Pole Switch, Back and Side-Wire, 15A 347V



Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see www.legrand.us/patents.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 20		

Technical Information

Actuator	Toggle	Contact Rating	347vac, 15amp
Amperage	15 A	Action	DPDT
Number of Poles	Double Pole	Voltage	347.0 V