



Pass and Seymour
Extra Heavy Duty Spec. Grade 347VAC Toggle Switch Back and Side Wire, Gray
Part No. PS371510GRY



Canadian 1-Pole Switch, Back and Side-Wire, 15A 347V

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007196030
Country Of Origin	Mexico	Switch Type	Toggle
Application Sector	Industrial	Standard	UL 20
Type	Switch		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		

Technical Information

Contact Rating	15amp, 347vac	Amperage	15 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Wattage	1 W	Voltage	347.0 V