



Pass and Seymour
Discontinued - Extra Heavy Duty Spec. Grade 347VAC Toggle Switch Back and Side Wire, Ivory
Part No. PS372010I

Canadian 1pole Switch, Back & Side Wire, 20amp 347volt, Ivory



Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see www.legrand.us/patents.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 20		

Technical Information

Actuator	Toggle	Contact Rating	347vac, 20amp
Amperage	20 A	Action	DPDT

Number of Poles	Double Pole	Voltage	347.0 V
-----------------	-------------	---------	---------