



Pass and Seymour
Extra Heavy Duty Spec. 347VAC Toggle Switch Back and Side Wire, Light Almond
Part No. PS372030LA



Canadian 1-Pole Switch, Back and Side-Wire, 20A 347V

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007196276
Country Of Origin	Mexico	Switch Type	Toggle
Application Sector	Industrial	Type	Switch

Technical Information

Contact Rating	20amp, 347vac	Amperage	20 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Voltage	347.0 V		
