



**Pass and Seymour**  
Series 16 In-Line Connectors  
Part No. PS40FBBL

400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow



### Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance

Exceptional seal for maintaining NEMA Type 3R and 4 integrity

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity

Heavy-duty hex set screws allow greater termination torque

Copper wire provides quality strain relief

Copper shim bundles wire strands to reduce "splaying."

### Specifications

#### General Info

|                    |                       |              |                |
|--------------------|-----------------------|--------------|----------------|
| Color              | Blue                  | UPC Number   | 785007308181   |
| Country Of Origin  | Mexico                | Product Line | Pass & Seymour |
| Application Sector | Commercial/Industrial | Standard     | UL, cCSAus     |

#### Technical Information

|                 |             |                          |  |
|-----------------|-------------|--------------------------|--|
| Number of Poles | Single Pole | Voltage                  | 600 V  |
| Wire Size       | 2/0 - 4/0   | Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4 |