



400A 600V F THREAD STUD PANEL MNT

Features & Benefits

Nylon housing provides outstanding impact and chemical resistance. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity.

Heavy-duty hex set screws (available on double set screw version only) allow greater termination torque.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007422573	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL, cUL

Technical Information

Connection	Threaded	Amperage	400 A
Wire Size	4/0	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4