

400A 600V MALE CAM TS PNL MT



Features & Benefits

Nylon housing provides outstanding impact and chemical resistance. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws (available on double set screw version only) allow greater termination torque.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-----------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Mexico | Application Sector | Commercial/Industrial |
| Standard | UL, cUL | | |

Technical Information

| | | | |
|--------------------------|--|----------|---------|
| Connection | Threaded | Amperage | 400 A |
| Wire Size | 4/0 | Voltage | 600.0 V |
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4 | | |