



Pass and Seymour
100A 3 Pole 4 Wire Non-Fusible Mechanical Interlock
Part No. PS4100MIR7W



Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 100 amp, 3, 480 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Color	Gray	UPC Number	785007015652
-------	------	------------	--------------

Country Of Origin	United States	Product Line	Pass & Seymour
-------------------	---------------	--------------	----------------

Application Sector	Commercial	Standard	UL Listed
--------------------	------------	----------	-----------

Technical Information

Number of Poles	3-Way	Voltage	480 V
-----------------	-------	---------	-------

Phase	3	Wire Size	2Awg
-------	---	-----------	------

Number of Wires	4
-----------------	---