



Pass and Seymour
15A, 125V Extra-Hard Use Hospital-Grade Angled Plug, Black and Clear
Part No. PS5266HGAN



Straight Blade Plug 2-Pole 3-Wire 15A 125A

Features & Benefits

Angle plugs and adapters both allow for 4-position face rotation.

Angle adapter (sold separately as catalog number EHU15AN) will accommodate all Pass & Seymour EHU-style Straight Blade plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.

Tri-drive assembly and cord-grip screws are standard on all angle adapters.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Type	Straight Blade

Dimensions

Product Width US	1.53 in	Product Depth US	1.35 in
Product Height US	2.13 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG
Voltage	125.0 V		
