



Pass and Seymour
30A 4 Pole 5 Wire Fusible Mechanical Interlock
Part No. PS530FMIR5W



Four pole, Five wire Fusible Mechanical Interlock Receptacle. 7.5 HP Standard, 20 HP Max. 3 amp, 600 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007101164	Country Of Origin	United States

Dimensions

Product Width US	9.13 in	Product Depth US	9.53 in
Product Height US	24.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E31169	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	30 A
----------	------