



Pass and Seymour  
MaxGrip M3 Plug, Gray  
Part No. PS5364GRY

Straight Blade Plug 2-Pole 3-Wire 20A 125V



## Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Enclosed terminals provide solid, internally-clamped connections.

High-visibility yellow and orange, or gray.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Molded finger grips promote safe, sure handling.

Hospital Grade version displays the Hospital Grade green dot.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL498	Type	Plug Tail

### Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Height US	1.83 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	18 - 12 AWG	Voltage	125.0 V

---