

Straight Blade Plug 2-Pole 3-Wire 20A 125A



## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Rugged two-piece cord grip provides more uniform cord retention.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Nylon housing provides impact and chemical resistance.

Internal dust shield keeps terminals free of contaminants.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Standard	UL 498
Type	Straight Blade		

### Dimensions

Product Width US	1.358 in	Product Length US	1.752 in
------------------	----------	-------------------	----------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

---

Product Environmental Profile      Yes

---

**Technical Information**

---

Connection	Wire Grounding	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	4	Voltage	125.0 V

---