



Straight Blade Connector 2-Pole 3-Wire 20A 125A

Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Enclosed terminals provide solid, internally-clamped connections.

High-visibility yellow and orange, or gray.

For covering patents, see www.legrand.us/patents.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Molded finger grips promote safe, sure handling.

Hospital Grade version displays the Hospital Grade green dot.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|----------------|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL Listed | Type | Straight Blade |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.34 in | Product Depth US | 1.21 in |
| Product Height US | 1.83 in | | |

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 20 A |
|-----------------|---|----------|------|

Number of Poles

Double Pole

Wire Size

18 - 10 AWG

Voltage

125.0 V
