



Straight BladeGCM PLUG 3W 20A 250V

## Features & Benefits

- Integral indication of ground continuity and power status. Continuous monitoring enhances personnel safety and adds convenience.
- Dual, bright LED indicators with 360 degrees visibility. Green LEDs indicate proper ground continuity and power status. Red LEDs indicate ground continuity loss or reversed polarity. No LED indicates open hot, open neutral, or hot to ground cross.
- For 250V configurations: Hot to ground cross will be indicated by a green and red LED.
- Chemical- and impact-resistant nylon housing features horizontal, easy-grip ribs on back body.
- Exclusive two-piece cord grip accepts a wide range of cord widths. Provides more consistent pressure for superior conductor retention.
- Internal dust shield keeps terminals free of contaminants.
- Recessed cord-grip screw reduces screwdriver slippage, improves safety. Quick-thread tri-drive assembly and cord-grip screws come backed-out and ready-to-wire.
- Color-coded terminal screws are positioned on the same plane and backed-out for fast installation.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- Add an EHU15AN for angled applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007237245	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL498, FDSPEC

Type	Plug Tail		
Dimensions			
Product Width US	1.516 in	Product Length US	1.752 in
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	18 - 12 AWG		