



Pass and Seymour  
MaxGrip M3 Connector, Gray  
Part No. PS5969GRY



Straight Blade Connector 2-Pole 3-Wire 15A 125V

## Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007237566	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL listed

### Dimensions

Product Width US	1.34 in	Product Depth US	1.21 in
Product Length US	1.83 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 0 AWG

---