



Decorator Combo Switch

Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Commercial	Standard	cULus UL20

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Contact Configuration	N-0	Operating Cycles	50000
Connection	Back and side wire	Contact Rating	20 Amp, 277 VAC
Amperage	20 A	Action	{3} SP
Number of Poles	Single Pole	Voltage	277.0 V
Environmental Conditions	Flammability: UL94 V2		
