



Pass and Seymour  
15A, 125V Hospital-Grade MaxGrip M3 Connector, Gray  
Part No. PS8119



STR BLD CONN 3W 15A125A HG

## Features & Benefits

Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements: arc resistance exceeds UL requirements.

Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws: close hinge housing around cord and tighten housing screws.

Enclosed terminals provide solid, internally-clamped connections.

Molded finger grips promote safe, sure handling.

High-visibility yellow and orange, or gray.

Hospital Grade version displays the Hospital Grade green dot.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | White      |
| Country Of Origin | Mexico         | Application Sector | Commercial |
| Standard          | UL 498         |                    |            |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Wires | 3           | Amperage  | 15 A        |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |

---

Voltage

125.0 V

---