



Pass and Seymour
15A 125V Heavy Duty Hospital-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. PS8200HRED



Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
---------------------	--------------------------	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Voltage	125.0 V
---------	---------
