



Spec Grade Decorator Combination Hallway Light & Single Receptacle Back & Side Wire 20amp 120/125VAC Light Almond

Features & Benefits

Impact-resistant face and body.

External screw-pressure-plate back and side wired.

Ground screw position under the end of the strap minimizes the risk of contact.

Sensor automatically turns light ON in the dark.

Light sensor for enhanced sensitivity.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

GE Lexan: high impact-resistant lens.

Accepts #12 and #14 AWG.

Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.

Increased light output for better illumination.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	NTL885TRLACC6
Country Of Origin	China	Application Sector	Commercial
Standard	cULus UL498		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Back and side wire	Amperage	20 A
Number of Poles	Double Pole	Voltage	120.0 V
Environmental Conditions	Flammability: UL94 V2		