



Pass and Seymour

Discontinued - Spec Grade Decorator Combination Hallway Light and Single Receptacles, Back and Side Wire, 20A, 120/125VAC, Light Almond

Part No. PS8HWLLA



Spec Grade Decorator Combination Hallway Light & Single Receptacle Back & Side Wire 20amp 120/125VAC Light Almond

Features & Benefits

Impact-resistant face and body.

GE Lexan: high impact-resistant lens.

External screw-pressure-plate back and side wired.

Accepts #12 and #14 AWG.

Ground screw position under the end of the strap minimizes the risk of contact.

Energy-efficient LED has average 20-year life expectancy: eliminates bulb replacement.

Sensor automatically turns light ON in the dark.

Increased light output for better illumination.

Light sensor for enhanced sensitivity.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	NTL885TRLACC6
Country Of Origin	China	Application Sector	Commercial
Standard	cULus UL498		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Back and side wire	Amperage	20 A
Number of Poles	Double Pole	Voltage	120 V
Environmental Conditions	Flammability: UL94 V2		