Pass and Seymour
15A NEMA L615 Plug - Black Back, White Front Body
Part No. PSL615P

15A 250V Extra-hard Use (ehu) Turnlok Registered Back Front Body

Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6/6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007236590	Country Of Origin	Mexico
Product Type	Plug	Features	Locking
Application Sector	Industrial	Standard	UL 498, FEDSPEC
Warranty Type	1-Year		

Dimensions

Product Height US	1.358 in	Product Length US	2.617 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Additional Information

Product Environmental Profile	Yes

Technical Information

Connector Style	Locking	Flanged	No
Terminal Accommodation	#4 AWG	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	L6-15P
Voltage	250.0 V		