



Vantage
DIN Controller Power Supply 36VDC
Part No. PSU36-DIN-I



The PSU36-DIN is a 36VDC, 130W DIN-rail-mounted power supply designed specifically for the Vantage InFusion DIN Controller (IC-DIN-II). Engineered to meet stringent power quality standards, it delivers quiet, reliable, and stable power for automation and control applications.

Features & Benefits

DIN rail mounting

36VDC power for the IC-DIN-II

Specifications

General Info

Product Line	Vantage	Color	Black
UPC Number	840624140757	Country Of Origin	United States
Installation Location	Enclosure	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Power Supply

Dimensions

Product Width US	7.5 in	Product Depth US	1.9 in
Product Height US	4.375 in		

Listing Agencies / 3rd Party Agencies

CE Certified	Yes
--------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Output Voltage	36 VDC	Load Rating	2.8 A @ 100/240 VAC
Compatibility	IC-DIN-II	Input Voltage	100 to 240 V
Line Frequency	50 Hz, 60 Hz	Indoor/Outdoor	Indoor
Mounting Type	DIN Rail	Connection Type	Screw Terminal
