



Pass and Seymour
PlugTail® Single Pole 15A Toggle Switch, Black
Part No. PT15AC1BK



PlugTail® Single-Pole 15A Toggle Switch

Features & Benefits

One-piece nickel-plated mounting strap for superior corrosion resistance

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Glass-reinforced nylon back body for durability and strength.

Shallow design for easier installation.

For covering patents, see www.legrand.us/patents.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

No exposed terminals create a finger safe application before, during, and after installation.

Heavy-duty bumpers for quiet, smooth operation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007026252
Country Of Origin	Mexico	Features	PlugTail
Switch Type	Toggle	Number of Switches	1
Application Sector	Commercial, Industrial	Wall Plate Included	No

Standard	FEDSPEC	Warranty Type	1-Year Limited Warranty
Type	Switch		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Gangs	1	Throw Type	Single Throw
Amperage	15 A	Number of Poles	Single Pole
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	PlugTail
Voltage	120/277 V		