




Pass and Seymour
PlugTail® Hospital Grade Tamper-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Ivory
Part No. PT2097HGTRI



PlugTail® Hospital-Grade Tamper-Resistant 20A Self-Test GFCI Receptacle. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Plated steel wrap strap design for maximum durability and corrosion resistance.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007048537
Country Of Origin	China	Number of Receptacles	2
Outlet Type	GFCI, Self-Test, Tamper-Resistant	Application Sector	Commercial, Hospital Grade
Standard	cULus, UL Listed, FSUL	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
Product Height US	4.2 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor