



Pass and Seymour
PlugTail® Specification Grade Illuminated 20A Toggle Switch, Clear
Part No. PT20AC1CSL



Single-Pole Illuminated Toggle Switch, 20A 120/277V For detailed PlugTail information, visit our PlugTail Headquarters.

Features & Benefits

One-piece nickel-plated mounting strap for superior corrosion resistance

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Glass-reinforced nylon back body for durability and strength.

Shallow design for easier installation.

For covering patents, see www.legrand.us/patents.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

No exposed terminals create a finger safe application before, during, and after installation.

Heavy-duty bumpers for quiet, smooth operation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Clear |
| Country Of Origin | Mexico | Application Sector | Residential/Commercial |
| Standard | UL 20 | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------|-------------|----------------|-------------------|
| Actuator | Toggle | Contact Rating | 20amp, 120/277vac |
| Amperage | 20 A | Action | DPDT |
| Number of Poles | Double Pole | Voltage | 120.0 V |
