



Pass and Seymour
PlugTail® Single Pole 20A Toggle Switch, White
Part No. PT20AC1W



PlugTail® Single-Pole 20A Toggle Switch

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	cULus, WS8996		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

Product Height US	2.375 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	120/277vac, 20amp	Closed Contact Resistance	Toggle
----------------	-------------------	---------------------------	--------

Amperage	20 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Wattage	1 W	Voltage	120.0 V
---------	-----	---------	---------