



Pass and Seymour
PlugTail® Three-Way 20A Toggle Switch, Brown
Part No. PT20AC3



PlugTail® 3-way 20A Toggle Switch

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007108095
Country Of Origin	Mexico	Switch Type	Toggle
Application Sector	Industrial	Standard	UL 20, FEDSPEC

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Amperage	20 A	Number of Poles	3-Way
Wire Size	#14 - #10 AWG		