



PlugTail® Single-Pole 15A Decorator Switch

Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtails

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007000887
Country Of Origin	Mexico	Features	Decorator Style
Application Sector	Industrial	Standard	UL 20
Type	Switch		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	15Amp, 120/277Vac	Amperage	15 A
----------------	-------------------	----------	------

Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Voltage	120/277 V		