



PlugTail® Single-Pole 20A Decorator Switch

Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtails

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 20		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Contact Rating	20amp, 120/277vac	Amperage	20 A
Wattage	1 W	Voltage	120.0 V