



Pass and Seymour
PlugTail® Single Pole 20A Decorator Switch, Gray
Part No. PT2621GRY



PlugTail® Single-Pole 20A Decorator Switch

Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtails

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007000689
Country Of Origin	Mexico	Features	Decorator Style
Application Sector	Industrial	Standard	UL 20
Type	Switch		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Voltage	120/277 V