



PlugTail® 3-way 20A Decorator Switch

## Features & Benefits

Ground wire pre-mounted to the box

4" square x 1 1/2" or 2 1/8" metal boxes

All Double Gang Kits contain two right angle PlugTail connectors

Mud ring factory installed

PlugTail Right Angle Connectors with 12 AWG copper pigtails

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 20

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Contact Rating	20amp, 120/277vac	Amperage	20 A
Wattage	3 W	Voltage	120.0 V