



Pass and Seymour  
**PlugTail® Decorator Split Circuit Spec Grade Receptacle, 20A, 125V, Black**  
Part No. PT26362SCBK

PlugTail® Decorator Split Circuit Spec Grade Receptacle, 20A, 125A



## Features & Benefits

.036 inch thick, brass, triple-ripe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Wire Size: #12 AWG THHN

Plated steel wrap strap design for maximum durability and corrosion resistance.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                    |                |                   |                      |
|--------------------|----------------|-------------------|----------------------|
| Product Line       | Pass & Seymour | Color             | Black                |
| UPC Number         | 785007000344   | Country Of Origin | Mexico               |
| Application Sector | Commercial     | Standard          | cULus UL498, FEDSPEC |

### Dimensions

|                                       |                          |                  |          |
|---------------------------------------|--------------------------|------------------|----------|
| Product Width US                      | 1.5 in                   | Product Depth US | 0.625 in |
| Product Height US                     | 2.75 in                  |                  |          |
| Listing Agencies / 3rd Party Agencies |                          |                  |          |
| cULus Listed                          | Yes                      |                  |          |
| Technical Information                 |                          |                  |          |
| Dielectric Strength                   | Withstands 2000V minimum | Number of Wires  | 3        |
| Temperature Rating                    | -40° - 60° C             | Amperage         | 20 A     |
| Number of Poles                       | Double Pole              | Wire Size        | 12 AWG   |
| Environmental Conditions              | Flammability: UL94 V2    |                  |          |