



Pass and Seymour  
**PlugTail® 15A 125V Heavy-Duty Spec Grade Single Receptacles, Gray**  
Part No. PT5261GRY



Plugtail Heavy-Duty Spec Grade Single Receptacles with Side and Back Wire install 5x faster than conventional wiring devices.

In the world of commercial wiring device installation, it's all about flexibility. For years now, PlugTail® electrical wiring devices have been providing that flexibility in commercial buildings everywhere. Easy to install, change out and upgrade, PlugTail allows you to continuously reconfigure to meet a building's electrical requirements as the space transforms – without the time and expense of rewiring. It's a cost-effective, code-compliant, proven way to keep your customers connected to the future, while securing your reputation as a forward-thinking electrical contractor.

## Features & Benefits

- PlugTail Devices install up to 5 times faster than traditional devices.
- No exposed terminals create a finger-safe application before, during and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing.
- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- Impact-resistant nylon face and thermoplastic back body.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Glossy	UPC Number	785007437874
Country Of Origin	Mexico	Receptacle Type	Straight Blade
Number of Receptacles	1	Outlet Type	Commercial
Application Sector	Commercial	Standard	UL UL498, CSA No.C22.2, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet, Plug Tail, Single

### Dimensions

Product Width US	1.546 in	Product Depth US	1.9 in
------------------	----------	------------------	--------

Product Height US	4.185 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Seismic Tested	No	Amperage	15 A
----------------	----	----------	------

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---